

# YZ15S series



- Specializing in small flow, stable flow rate, precise and superior performance
- Single and dual channel optional
- Knob switch design, easy to open and close, convenient tube installation
- Small size, compact structure design
- Can be matched with various types of hoses and motors

Typical Application: applicable to dental implants and analytical instruments.


Max speed : 300rpm

Max flow | YZ15S-1:380mL/min  
YZ15S-2:185mL/min/Channels


Model	Pump Head	Motor	Voltage	Max Speed	Max Flow(mL/min)				
					13#	14#	19#	16#	25#
UCP315-A2	YZ15S-1	Stepper		300	14.4	54	116	185	380
UCP315-A1	YZ15S-1	Stepper		300	14.4	54	116	185	380
OEM215	YZ15S-1	DC Gear	DC12V	300	14.4	54	116	185	380
ACM115	YZ15S-1	AC synchronous		100	4.8	18	38	61	126
UCP315-A2	YZ15S-2	Stepper		300	14.4	54	116	185	
UCP315-A1	YZ15S-2	Stepper		300	14.4	54	116	185	
OEM215	YZ15S-2	DC Gear	DC12V	300	14.4	54	116	185	
ACM115	YZ15S-2	AC synchronous		100	4.8	18	38	61	

Note: The test environment for flow data is normal temperature and pressure, and the test fluid is water. The values are for reference only, please refer to the actual situation.


UCP315-A2 (Max flow 380mL/min)




UCP315-A1 (Max flow 380mL/min)



OEM215 (Max flow 380mL/min)



ACM115 (Max flow 126mL/min)



Note: This series of pump head 42 DC motor is not suitable for PharMed BPT tube type

(Unit: mm)