CHONRY 创锐

LG350LC

PRODUCT DESCRIPTION

Batch transfer peristaltic pump

CHONRY 创锐

LG350LC

PRODUCT DESCRIPTION

Batch transfer peristaltic pump

Used in food industry, fluidized bed liquid supply, liquid medicine filtration, photovoltaic, Chemical and other fields.

Max flow 33000mL/min





LG350LC is a batch transmission type peristaltic pump. It adopts 3.5-inch color LCD touch screen display. The operation is simple and intuitive. It has four working modes: timing, quantitative, timing quantitative, and transmission. It can be intelligently set according to different work needs, and the motor torque is strong., suitable for KZ50 pump head, the maximum

LG350LC

flow can reach 33L, support RS485/MODBUS and other remote control modes.

Multiple modes With timing, quantitative, timing

with timing, quantitative, timing quantitative, transmission four working modes.

Power off save

Can automatically save the control parameters when the last power failure.

Data storage

9 sets of data can be stored for users.



LCD touch

3.5-inch color LCD, Chinese and English display, touch screen control.

Very large flow

Compatible with KZ50 pump head, the maximum transmission flow can reach 33L/min.


Support external control

Support RS485/MODBUS communication protocol, analog control, foot switch control.


Drive model	LG350LC
Max speed	350rpm (reversible)
Max flow	33000mL/min
Speed resolution	0.1rpm
Speed mode	Touch screen adjustment
Display method	Color LCD display (Chinese and English optional)
Suction angle	10°-720°
Suction speed	10-300rpm
Power supply	AC220±10% (Standard) or AC110V±10% (optional)
Power	<750W
External control interface	DB-15
External control method	Start control/direction control/speed control (0-5V, 0-10V, 4-20mA optional) RS485 serial communication
Ambient temperature	0-40 °C
Drive size	340X242X342.5(mm)
Protection class	IP31 (indoor use, avoid prolonged exposure to UV rays)

Schematic diagram of structure and function

 $\mathsf{Pump head} \ \rightarrow \ \mathsf{Coupling} \ \rightarrow \ \mathsf{Pump head} \ \mathsf{connection plate} \ \rightarrow \ \mathsf{Driver}$



Coupling



(Unit: mm)

CHONRY 创锐

Baoding Chuangrui Precision Pump Co.,Ltd.

Address: NO.369 of HuiYang Street , Baoding 071000,Hebei , China Mobile: +86 15633705132 Website: http://www.crpump.com Email: support@crpump.com