

SG600FC PRODUCT

DESCRIPTION

Large flow intelligently controlled distribution peristaltic pump



CHONRY 削销

SG600FC

PRODUCT DESCRIPTION

Large flow intelligently controlled distribution peristaltic pump

It is used in large-flow sub-packaging in pharmaceutical factories, chemicals, food, chemical environmental protection, etc.

Max flow 12000mL/min

Max speed 600rpm





SG600FC

SG600FC is a large flow intelligently controlled distribution peristaltic pump. Using a 3.5-inch color LCD touch screen display, the operation is simple and intuitive. It has two working modes: transmission and distribution. It can be intelligently set according to different working needs. The motor has strong torque and is suitable for YZ35, YZ35-13L and YZ35LS pump heads. It can be used for Data storage, supports RS485MODBUS and other remote control modes.

Multiple modes

It has two working modes of transmission and distribution, and can perform repeated timing and quantitative filling

LCD touch

3.5-inch color LCD, Chinese and English display, touch screen control

Adapt to multiple pump heads

YZ35, YZ35-13L, YZ35LS pump heads can be installed, and the pump heads can be cascaded



Suction function

The speed angle of reverse operation can be customized to prevent liquid dripping

Data storage

8 sets of data can be stored for users

Support external control


Support RS485MODBUS communication protocol, analog control, foot switch control

Technical parameter

Drive model	SG600FC
Max Speed	600rpm (reversible)
Speed resolution	0.1rpm
Max flow	12000mL/min
Speed mode	Touch screen adjustment
Display method	Color LCD display (Chinese and English optional)
Suction angle	10°-720° (0° means no back suction)
Suction speed	10-300rpm
Power supply	AC220V±10% (standard) or AC110V±10% (optional)
Power	<400W
External control interface	DB-15
External control method	Start control/direction control/speed control (0-5V, 0-10V, 4-20mA optional) RS485 serial communication
Drive size	340X238X325.5(mm)
Protection class	IP31 (indoor use, avoid prolonged exposure to UV rays)


Schematic diagram of structure and function


 $\mathsf{Pump}\;\mathsf{head}\;\mathsf{screw}\;\to\mathsf{Pump}\;\mathsf{head}\;\to\mathsf{Coupling}\;\to\mathsf{Pump}\;\mathsf{head}\;\mathsf{connection}\;\mathsf{plate}\;\to\mathsf{Driver}$




Dimensions

SG600FC







(Unit: mm)

* Technical parameters are subject to change without notice.

CHONRY创锐

Baoding Chuangrui Precision Pump Co.,Ltd.

Address: NO.369 of HuiYang Street , Baoding 071000, Hebei , China

Mobile: +86 15633705132

Website: http://www.crpump.com Email: support@crpump.com

